

ColorTherm™ insulated colored glass units add beauty and elegance to your designs



Light Blue



Cobalt Blue



Light Green



Yellow



Translucent White

The actual color of the glass may differ from the representation above.

- Body-colored, not tinted
- Available in four transparent designer colors and translucent white
- Colored glass is fire-polished on both sides
- All glass is fully tempered
- Includes low-E coating on side three
- Total thickness of insulated glass package: 1 inch
- Maximum sizes:
 - All colors except cobalt blue: 91" x 56"
 - Cobalt blue: 80" x 56"
- Suitable for exterior and interior applications

ColorTherm™ insulated colored glass performance data*

ColorTherm IGU Type	U Value (BTU)	UV Light Transmission	Visible Light Transmission	Solar Heat Gain Coefficient	Shading Coefficient
Dark Cobalt Blue 13/64" (5 mm) Cobalt outer lite	0.28	0.13	0.03	0.19	0.22
Light Blue 1/4" (6 mm) Light blue outer lite	0.28	0.11	0.30	0.26	0.30
Light Green 1/4" (6 mm) Light green outer lite	0.28	0.11	0.36	0.32	0.37
Light Yellow 1/4" (6 mm) Light yellow outer lite	0.28	0.02	0.45	0.37	0.43
Translucent White 1/4" (6 mm) White outer lite	0.28	0.03	0.14	0.21	0.25

All insulated glass units are one-inch overall thickness, have a 12-mm air-filled cavity, include 1/4" thick float glass as the inner lite.

*Custom thermal values can be supplied upon request.

For additional information, please contact:

Architecture
SCHOTT North America, Inc.
 555 Taxter Road
 Elmsford, NY 10523

Phone: 914.831.2240
 Fax: 914.831.2346
 E-mail: architecture@us.schott.com
www.us.schott.com/architecture

