




SCHOTT TO PLUS®

Product Information

SCHOTT TO PLUS® is a TO header with enhanced performance for high speed data rates of 10Gbit/s and above. In a recent breakthrough the same line of headers was further tweaked and proven to have worked at data rates of 17Gbit/s. Through this breakthrough, in which the bandwidth of a TO is enhanced, end users are now able to keep costs in check by utilizing the existing infrastructure of assembly and manufacturing. With the use of the TO PLUS® transceiver, manufacturers need not resort to complex flat or ceramic packages.

Advantages

- Hermetically sealed using proven glass-to-metal sealing technology:** TO headers have been used in the market for several decades due to their proven reliability and performance. The TO PLUS® header line utilizes the same technology to deliver the same kind of reliability.
- Excellent RF Performance:** With matched impedance the headers are able to have low insertion and return losses for high data rates of 10Gbit/s and above.
- Existing Outlines:** Since the enhancement is achieved by a combination of glass, pins and placement only, a TO PLUS® can be built from any existing outline of TO headers, such as TO46, TO56, TO38, etc. This allows end users to utilize the same mating optical caps and manufacturing techniques / infrastructure.
- One-stop-shopping** due to vertically integrated manufacturing, from materials to components.



No responsibility can be taken for the accuracy of this information. Despite the fact that all reasonable care was taken in presenting and keeping this information up to date, SCHOTT neither accepts legal responsibilities nor guarantees the completeness, accuracy and up-to-dateness of the information presented here.

Preliminary Specifications	
Platform:	TO PLUS®
Outlines:	TO46, TO56, TO38, Custom TO
Impedance:	25 Ω / 50 Ω / 100 Ω
	Single / Differential
Return Loss S11 @ 10Ghz	< -20 dB
Insertion Loss S21 @ 10Ghz	> -1 dB

Applications	
10G Headers for VCSEL's in Fiber Channel 4G / 8G	
For LAN / Gigabit Ethernet Applications	
17G Fiber Channel	

For more information:

SCHOTT Electronic Packaging

A Division of SCHOTT North America, Inc.
 122 Carlton Street
 Southbridge, MA 01550
 USA

Phone: +1 508 765-3370
 Fax: +1 508 765-3377
 epackaging@us.schott.com
 www.us.schott.com/epackaging

SCHOTT
 glass made of ideas