


# Design rule for Low Temperature Cofired Ceramics (LTCC) substrate

## Packages for:

- Radar applications
- High frequency applications



## Materials Data:

		mark	standard	tolerance	special	tolerance
Structure Parameters	Length	X	5 - 25	± 1%	2 - 50	± 0.5%
	Width	Y	5 - 25	± 1%	2 - 50	± 0.5%
	Substrate Thickness	Z	0.4 - 3	± 7%	0.2 - 5	± 0.2%
	Layer Thickness	A	0.12, 0.2, 0.25 0.32, 0.4, 0.5	± 10%	0.1	± 5%
	Flatness (as-fired)				0.05 / 10 mm	
	Flatness (machined)				0.005 / 10 mm	
Vertical Interconnects	Filled Via					
	Typical Diameter	B	0.18		0.1	
	Diameter Range		0.15 - 0.3		0.1 - 0.5	
	Via-to-Via Centerline	L	1		0.6	
	Via-to-Edge	M	thickness + via diameter			
	Bore Coated Via					
	Typical Diameter (ID)	C	0.4			
Diameter Range		0.4 - 0.8				
Internal Metal Circuit	Line Width (without via)	D	0.08	± 20 %	0.07	
	Line-to-Line Space (far from via)	E	0.08	± 20 %	0.07	
	Line Width (with via)	G	0.25	± 20 %	0.2	
	Line-to-Line Space (near via)	H	0.2	± 20 %	0.2	
	Space from edge	F	0.7		0.5	
Surface Metal Circuit	Line Width (without via)	G	0.1	± 20 %	0.08	
	Line-to-Line Space (far from via)	H	0.1	± 20 %	0.08	
	Line Width (with via)	G	0.3	± 20 %	0.2	
	Line-to-Line Space (near via)	H	0.25	± 20 %	0.2	
	Space from edge	K	0.4		0	

unit: mm, %

## For more information:

### SCHOTT Electronic Packaging

A Division of SCHOTT North America, Inc.  
122 Charlton Street  
Southbridge, MA 01550  
USA

Phone: +1 508 765-3370  
Fax: +1 508 765-3377  
epackaging@us.schott.com  
www.us.schott.com/epackaging

**SCHOTT**  
glass made of ideas