

Housings for High Heat Load Applications

Product Information

High power lasers, often found in medical and industrial applications, require high power input and generate high levels of heat. Hence, materials used in the encapsulation of the laser must be capable of carrying high current levels to support the functioning of the laser and have high thermal conductivity so as to dissipate heat quickly.

SCHOTT offers a variety of laser packages, including a 9-mm TOP header for high power laser applications. This stamped TO header, which is available in two standard designs, is a straightforward packaging option. Customers can, thereby, utilize accessible manufacturing infrastructure to achieve economies of scale.

Advantages

- **High thermal conductivity:** Copper, which possesses high thermal conductivity to support rapid heat dissipation, is used as the base material.
- **High current carrying capacity:** With the use of readily available material such as CF25, the TO header can carry high current levels.
- **Customizable:** In addition to two standard stamped designs, SCHOTT can create modified TO headers or packages with similar properties.
- **Hermeticity, if required:** In cases whereby hermeticity is requested, headers can be modified with CRS base and copper heatsink.

Preliminary Specifications


| | |
|---------------------------|--|
| TO header size | 9 mm (standard) Customizable |
| Thermal conductivity | 401 W · m ⁻¹ · K ⁻¹ (Copper) |
| Current carrying capacity | 4A @ 0.45mm (0.018") pin diameter |
| Pin material | CF25 |
| Eyelet material | Copper |
| Finish | Electroless Ni Electroless Ni + Electrolytic Au |

For more information:


SCHOTT Electronic Packaging

A Division of SCHOTT North America, Inc.
122 Charlton Street
Southbridge, MA 01550
USA

Phone: +1 508 765-3370
Fax: +1 508 765-3377
epackaging@us.schott.com
www.us.schott.com/epackaging



Two standard, stamped 9-mm TO header designs from SCHOTT for high heat load applications



Current carrying capacity of
— CF25 and — Copper