

A08616



Reflector Ring, A08616

Ringlight Reflector Rings

A08616 Reflector Ring Features


Reflector ring creates special lighting effects.

- Illuminates scratches on highly reflective surfaces.
- The A08616 reflector ring fits our Universal and 66 mm series of ringlights. See chart below for part numbers.
- The A08616 reflector ring comes in two separate parts; the retaining ring and the reflector ring. The reflector ring drops inside the retaining ring which snap-fits onto the ringlight.
- The reflector ring is made of mirror polished aluminum. The retaining ring is made of aluminum with a black anodized finish.

Ringlight Reflector Rings

Part No.	Ringlights
A08616	A08600, A08603, A08604, A08620, A08625, A08680, A08600.1

A08614



Anti-Slip Ringlight Clamps, A08614

Ringlight Support Apparatus

For accurate positioning when using fiber optic components in industrial and laboratory environments.

Support Apparatus

Holders, Clamp Rings, and Anti-slip Pads

Part No.	Description
A08614	Anti-slip Ringlight Clamps for ringlight models A08600, A08620. (3 clamps in package)

