

B3 Fiber

Product improvements may result in specification or feature changes without notice.


Material: Glass

Characteristics: Excellent transmission, performs best in visible spectrum, high acceptance angle and extremely colorless.

Specifications:

Numerical Aperture NA:	0.54
Acceptance angle:	65°
Color temperature (D 65 illumination) :	5870 K
Fiber diameter (µm):	30,50,70
Bundle length (M):	≤10

Spectral Transmission for 1 M Bundle, Fiber Type A2



Lighting and Imaging

SCHOTT North America, Inc.

122 Charlton Street

Southbridge, MA 01550

USA

Phone: +1508/765-9744

Fax: +1508/764-6273

E-mail: lightingimaging@us.schott.com

www.us.schott.com/lightingimaging

SCHOTT
glass made of ideas