


# PCS Fiber

**Material:** Plastic Clad Silica (PCS)

**Characteristics:** High OH. Performs good in visible spectrum. Economic alternative to Fused Doped Silica.

<b>Specifications:</b>	Numerical Aperture NA:	Short Lengths (<2 M) 0.40 Long Lengths (>40 M) 0.30
	Acceptance angle:	Short 47° Long 35°
	Fiber diameter (μm):	275
	Bundle length:	Quoted



# PCS Fiber


Product improvements may result in specification or feature changes without notice.

**Material:** Plastic Clad Silica (PCS)

**Characteristics:** Low OH. Performs good across UV, visible, and IR spectrum.  
Economic alternative to Fused Dope Silica.

<b>Specifications:</b>	Numerical Aperture NA:	Short Lengths (<2 M) 0.40 Long Lengths (>40 M) 0.30
	Acceptance angle:	Short 47° Long 35°
	Fiber diameter (µm):	275
	Bundle length:	Quoted

**Spectral Transmission for 1 M Bundle, Fiber Type PCS Low OH**



Lighting and Imaging  
**SCHOTT North America, Inc.**  
122 Charlton Street  
Southbridge, MA 01550  
USA  
Phone: +1508/765-9744  
Fax: +1508/764-6273  
E-mail: [lightingimaging@us.schott.com](mailto:lightingimaging@us.schott.com)  
[www.us.schott.com/lightingimaging](http://www.us.schott.com/lightingimaging)

**SCHOTT**  
glass made of ideas