

W Fiber

Product improvements may result in specification or feature changes without notice.


Material: Glass

Characteristics: Used for the visible region of the spectrum when a wide aperture angle is required.

Specifications:

Numerical Aperture:	0.87
Acceptance angle:	119°
Color temperature (D 65 illumination):	4700 K
Fiber Diameter (μm):	30
Bundle length (M):	≤ 10

Note: Longer lengths available upon request



Lighting and Imaging

SCHOTT North America, Inc.

122 Charlton Street

Southbridge, MA 01550

USA

Phone: +1508/765-9744

Fax: +1508/764-6273

E-mail: lightingimaging@us.schott.com

www.us.schott.com/lightingimaging

SCHOTT
glass made of ideas