



Flexible light guide 2 branch



Flexible light guide 3 branch



Flexible light guide 2 branch randomized

Flexible Light Guides

2- and 3-branch

Features

- Flexible light guides are available in different lengths and diameters.
- Articulating arm and different holders for positioning available.
- Focusing lenses, color filters and polarizers available.
- Manufactured in the EU.


Benefit

High flexibility for different illuminations as well as remote illumination.

Flexible Light Guides, 2- and 3-branch										
Cold light source	Part-No.	Type	Length	End tip Ø	End tip length	Active Ø/ branch	Active Common end Ø	Jacketing material	Outer Ø Jacketing	Light source adapter Ø
			L	E	l	b	B		D	F
KL 200	171 202	2 branch	1000 mm	6 mm	20 mm	4.0 mm	5.5 mm	Megolon	6.5 mm	9 mm
KL 200 LED			39.37 inch	0.24 inch	0.79 inch	0.16 inch	0.22 inch		0.26 inch	0.35 inch
KL 1500*	155 204	2 branch	1000 mm	6 mm	20 mm	4.5 mm	6.4 mm	M-PVC	9.8 mm	10 mm
KL 2500 LCD			39.37 inch	0.24 inch	0.79 inch	0.18 inch	0.25 inch		0.39 inch	0.39 inch
KL 2500 LCD	155 205	3 branch	1600 mm	6 mm	20 mm	4.5 mm	6.4 mm	M-PVC	9.8 mm	10 mm
	39.37 inch		0.24 inch	0.79 inch	0.18 inch	0.25 inch	0.39 inch		0.39 inch	
KL 2500 LCD	155 206	3 branch	1000 mm	6 mm	20 mm	4.5 mm	7.8 mm	M-PVC	9.8 mm	10 mm
			39.37 inch	0.24 inch	0.79 inch	0.18 inch	0.31 inch		0.39 inch	0.39 inch
KL 2500 LCD	255 204	2 branch (randomized)	1000 mm	10 mm	20 mm	9 mm	12.8 mm	M-PVC	15.0 mm	18 mm
			39.37 inch	0.40 inch	0.79 inch	0.36 inch	0.51 inch		0.60 inch	0.71 inch

* LCD, compact, LED

Flexible Light Guides



Lighting and Imaging
SCHOTT North America, Inc.
122 Charlton Street
Southbridge, MA 01550-1960
USA

Phone: +1 508/765-9744
Fax: +1 508/764-6273
lightingimaging@us.schott.com
www.us.schott.com/lightingimaging

SCHOTT
glass made of ideas

For your local sales contact please visit
www.us.schott.com/lightingimaging