

SCHOTT® Wound Fiber Bundles

Ruggedized Flexible Imaging Applications



Performance Characteristics

Wound Fiber Bundles are coherent, flexible fiber optic bundles used in applications where images must be transferred from remote locations. These bundles are used in a wide range of applications, including industrial remote vision systems, ordered array detectors, hazardous environment imaging, defense and research.

Their numerical aperture is typically 0.63 and standard lengths range from 610 mm to 4500 mm.

SCHOTT can also produce custom image guide assemblies in vertical or horizontal formats required to meet nonstandard imaging applications.

Bundles come with standard "C" mount adaptors on each end.

Typical Bundle Specifications

Quality Area:	1.8 x 1.8 mm ² – 38 x 33 mm ² with custom capabilities
Format Size:	2 mm x 2 mm up to 40 mm x 35 mm
Single Fiber Size:	60 x 60 um, 10 um elements, 6 x 6 array
Numerical Aperture:	0.63
Resolution*:	45 lp/mm
Transmission:	40% @ 500 nm – 1200 nm
Bending Radius:	Determined by bundle diameter and sheathing
Temperature Resistance:	-40 °C to +125 °C (-40 °F to +257 °F)

We can also supply and custom design objective and relay lens.

* Resolution Measurement performed with an 1951 USAF Resolution Target using diffuse white light illumination. Resolution may vary with other wavelengths.



For more information please contact

Lighting and Imaging
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge, MA 01550

Phone: (508) 765 - 9744
 Fax: (508) 765 - 1299
lightingimaging@us.schott.com
www.us.schott.com/lightingimaging

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.

© SCHOTT North America, Inc.

SCHOTT
 glass made of ideas