


D 263[®] M Cover Glass


The cover glass type D 263[®] M is a colorless borosilicate glass which is produced by a SCHOTT specific down-draw method. It is available in different stock sheet sizes with thicknesses ranging from 0.1 mm to 0.21 mm.

D 263[®] M is a perfect choice as cover glass for microscopic analysis and meets the requirements specified in ISO 8255-1 and DIN ISO 8255-1.

The chemical composition of D 263[®] M ensures valid and reliable research results due to its low auto-fluorescence and high chemical resistance.



Applications



Cover glass in microscopy for medical, biological and research work

- High luminous transmittance
- Colorless appearance
- Excellent cosmetic quality
- Easy to cut using the scribe and break method
- Excellent flatness
- Resistant to chemical attack
- Refractive index finely adapted to microscopes
- Low auto-fluorescence
- Easy to separate in automatic coverslippers due to protective coating
- Tight thickness control
- Resistance to environmental conditions ensure high durability
- Good cell growth
- Thickness for high-performance applications available

Technical Data

Dimensions	410 mm x 435 mm, 410 mm x 415 mm, 410 mm x 710 mm
Thicknesses	0.10 mm up to 0.21 mm
Luminous transmittance τ_{vD65} (d = 0.15 mm)	91.7 %
Coefficient of mean linear thermal expansion α (20 °C; 300 °C) (static measurement)	$7.2 \cdot 10^{-6} \text{ K}^{-1}$
Transformation temperature T_g	557 °C
Dielectric constant ϵ_r at 1MHz	6.7
Refractive index n_D	1.5230
Refractive index n_e	1.5255
Density ρ (annealed at 40 °C/h)	2.51 g/cm ³

For more information please contact:

Advanced Optics
SCHOTT North America, Inc.
400 York Avenue
Duryea, PA 18642
USA

Phone: 1-570-457-7485
Fax: 1-570-457-7330
info.optics@us.schott.com
www.us.schott.com/advanced_optics

SCHOTT
glass made of ideas