

# D 263® T<sup>eco</sup> Thin Glass

D 263® T eco thin glass is a clear borosilicate glass that has a high chemical resistance and is produced by a SCHOTT specific down-draw method. It is available in a variety of thicknesses ranging from 0.03 mm to 1.1 mm.

D 263® T eco borosilicate glass is available in standard stock size sheets or can be custom cut into round or square shapes.

D 263® T eco thin glass is used as substrate glass for coatings or as replacement for plastic for applications in the automotive and electronics industries.

D 263® T eco is manufactured with eco-friendly refining agents.




## Applications



### Resistive touch panel for built-in car navigation

- Stable against sunlight and heat
- Not permeable to humidity
- Flexibility is similar to that of plastic
- Easy to cut by laser or scribe and break method



### Optocaps in laser diodes

- High luminous transmittance
- Easy to process
- Coefficient of thermal expansion match with metals for hermetic sealings



### Substrate glass for IR cut-off filter for camera modules in mobile phones

- High luminous transmittance
- Easy to dice by diamond saw
- Coatings adhere well due to excellent surface quality
- Smooth surface for coatings without previous polishing
- Range of thin thicknesses enables easy adaptation for future product miniaturization

## Technical Data

Dimensions	440 mm x 360 mm, other size on request
Thicknesses	0.03 mm up to 1.1 mm
Luminous transmittance $\tau_{vD65}$ (d = 1.1 mm)	91.7 %
Coefficient of mean linear thermal expansion $\alpha$ (20 °C; 300 °C) (static measurement)	$7.2 \cdot 10^{-6} \text{ K}^{-1}$
Transformation temperature $T_g$	557 °C
Dielectric constant $\epsilon_r$ at 1MHz	6.7
Refractive index $n_D$	1.5230
Density $\rho$ (annealed at 40 °C/h)	2.51 g/cm <sup>3</sup>

For more information please contact:

Advanced Optics  
SCHOTT North America, Inc.  
400 York Avenue  
Duryea, PA 18642  
USA

Phone: 1-570-457-7485  
Fax: 1-570-457-7330  
info.optics@us.schott.com  
www.us.schott.com/advanced\_optics

**SCHOTT**  
glass made of ideas