


NIR Cutoff Filters / Blue Filter Glass

A product family with two groups that have extraordinary properties



Used in numerous applications, NIR cutoff filters can be found just about everywhere we look in our modern lives. They are equipped to image sensors so that natural colors are produced, and they make digital cameras respond to light as our eyes do. Special NIR cutoff filters are required for any display or operation control when viewed at using a night vision system (NVIS compatible equipment), which are becoming more and more commonly used by police and rescue forces. Depending on the main application, our optical filter glass types are grouped into glasses for **mobile applications** and glasses for industry applications with **high steepness** of the NIR cutoff, respectively.

1. Group – Mobile applications

BG60, BG61, BG62, BG66, BG67, BG57 NEW

Designed to perform in difficult environments

SCHOTT's new IR filter glasses have been designed to perform in difficult environments. Equipped with a specified coating, these filters remain completely transparent for more than 1000 hours without any surface corrosion and deliver extraordinary image quality.



Advantages


- Repeatable optical performance due to mass production
- Excellent inner quality, e.g. low striae
- Allows true color imaging
- High NIR absorption at smaller thickness

Applications

- Medical
- Imaging
- Surveillance
- NVIS (night vision) compatible display
- Industrial applications

Forms of Supply

- Matt plates
- Polished filters
- Additional coating, framing and assembly available



		BG60	BG61	BG62	BG66	BG67	BG57
refractive index	n_e	1.5399	1.5370	1.5417	1.5430	1.5427	1.5547
	n_d	1.5379	1.5350	1.5397	1.5418	1.5405	1.5523
cutoff wavelength	$\lambda_{0.5}$	633 nm	648 nm	644 nm	634 nm	632 nm	634 nm
at thickness		@ 0.3 mm	@ 0.3 mm	@ 0.21 mm	@ 0.21 mm	@ 0.175 mm	@ 0.11 mm




2. Group – High steepness of NIR cutoff

BG18, BG38 – BG42, BG50, BG55, S8022, S8023, S8612

Designed to perform for high-precision optical applications

For decades, these glasses have been popular because of the excellent optical properties they provide. These optical properties include high transmission in addition to high blocking with a very narrow transition range. Furthermore, these glasses are ideal bandpass filters for visual areas when high absorption in the near infrared (NIR) wavelength range is required. The slope of the IR edge is exceptional, and guarantees a sharp distinction between visible light and NIR radiation.



	BG18	BG38	BG39	BG40	BG42	BG50	BG55	S8022	S8023	S8612
cutoff wavelength $\lambda_{0.5}$	595 nm	646 nm	603 nm	635 nm	595 nm	626 nm	596 nm	533 nm	565 nm	599 nm
at thickness	@ 1 mm									



Advantages

- Extraordinarily high transmittance in the visible range
- High NIR absorption
- Excellent inner quality, e.g. low striae
- Allows true color imaging

Applications

- Medical
- Imaging
- Surveillance
- NVIS (night vision)
- Industrial applications

Forms of Supply

- Polished filters
- Additional coating, framing and assembly available

Advanced Optics
 SCHOTT North America, Inc.
 400 York Avenue
 Duryea, PA 18642
 USA
 Phone +1 570/457-7485
 Fax +1 570/457-7330
 info.optics@us.schott.com

www.us.schott.com/advanced_optics

SCHOTT
 glass made of ideas