


New LASF35 ($n_d = 2,022$; $v_d = 29,06$)

Achieved combination of outstanding n_d and v_d values together with excellent transmittance especially in the blue spectral range makes LASF35 glass one of the most preferred optical materials for optical designs.

Characteristics

- Outstanding n_d and v_d values ($n_d = 2.022$; $v_d = 29.06$)
- Excellent transmittance even in the blue spectral range
- ROHS compliant



For more information please contact:

Advanced Optics
SCHOTT North America, Inc.
 400 York Avenue
 Duryea, PA 18642
 USA

Phone: +1 570/457-7485
 Fax: +1 570/457-7330
 info.optics@us.schott.com
 www.us.schott.com/advanced_optics

Applications

- Outstanding optical material for optical design, e.g. lenses for high performance digital cameras or other products and applications.
- LASF35 is the material of choice for ball lenses used in OptoCouplers due to its self-focusing characteristic and low attenuation.

SCHOTT LASF35 high index glass with superb transmittance in the blue

