

On the safe side

SCHOTT Radiation Shielding Glass RD 30®

A good, clear view

SCHOTT RD 30® is drawn, clear flat glass that contains lead and is used as radiation shielding glass. It has the usual surface traits of drawn glass.

Not only for use in mammography

RD 30® was developed especially for use in mammography workstations with weak X-rays (a lead equivalent of 0.5 mm Pb at 56 kV is commonly used here). Nevertheless, RD 30® also has a lead equivalent of 0.5 mm Pb at a higher tube voltage (up to 150 kV) and can therefore also be used in workplaces for material testing and at all other workplaces with weak X-ray radiation.

To ensure safe handling of the glass, we recommend that you follow our "Instructions on Installing, Cleaning and Caring for Radiation Shielding Glass."

Properties and processing options

The SCHOTT Radiation Shielding Glass RD 30® is delivered in processed or refined form.

The following processing options are available with RD 30®:

- Special formats, also with edge processing and bored holes
- Safety glass (tempered)
- Laminated glass
- Curved glass
- Printed/painted glass



Delivery forms – RD 30® Radiation Shielding Glass

- Single pane glass: 6 mm (max. delivery dimensions: 2,350 x 1,500 mm)
- Laminated glass: > 6 mm (consisting of 2 x 3 mm RD 30®)

Examples of applications

SCHOTT RD 30® Radiation Shielding Glass can be used in many areas of medicine, science and industry, in particular in X-ray rooms, operating rooms, irradiation stations, dental practices, radiology practices, laboratories and materials testing.

RD 30®: Lead equivalents in mm Pb and delivery dimensions of single pane glass

Thickness d mm	Attenuation equivalent in mm Pb and delivery dimensions:						Max. weight kg/m ²	Max. dimensions mm x mm
	50 kV	56 kV	76 kV	80 kV	110 kV	150 kV		
6.0 ± 0.25	≥ 0.5	≥ 0.5	≥ 0.5	≥ 0.5	≥ 0.5	≥ 0.5	20	2,350 x 1,500

Technical data on RD 30® (single pane glass)

Optical properties

Refractive index n_e at 20°C (annealed at 40°C/h) 1.579
Light transmission factor (d = 6.0 mm) 90.5%

Chemical properties

Hydrolytic class according to DIN ISO 719 HGB 3
Lead oxide content (PbO) ≥ 22%
Total heavy metal oxide content ≥ 23%

Mechanical characteristics

Density in g/cm³ (delivery condition) ≥ 3.13

Other properties

Glass thickness 6.0 mm
Evaluated sound insulation R_w
Spectral adaptation values C and C_{tr}
 $R_w(C; C_{tr}) = 34 (-2; -2)$ dB

Advanced Optics
SCHOTT North America, Inc.
555 Taxter Road
Elmsford, NY 10523
USA
Phone +1 (914) 831-2240
Fax +1 (914) 831-2346
info.architecture@us.schott.com

www.us.schott.com/architecture

SCHOTT
glass made of ideas