

# SCHOTT MIROGARD® – Anti-Reflective Glass for Art Glazing

## Technical Data Sheet

Dimensions (net/without dipping edge (min.))	Thickness / (Type)		Thickness tolerance	Standard box contents			Luminous reflectance	Luminous trans- mittance	UV trans- mittance	Color rendering index
	inches x inches	inches		inches	sq ft	Pieces				
<b>MIROGARD®</b>										
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 355	5 small-scale- packaging à 3 sheets, approx. 77 lbs	approx. 573	0.9	99	52	100
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 538	23	approx. 727	0.9	99	52	100
34 <sup>27</sup> / <sub>32</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 592	10 small-scale- packaging à 5 sheets, approx. 64 lbs	approx. 738	0.9	99	52	100
34 <sup>27</sup> / <sub>32</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 538	46	approx. 683	0.9	99	52	100
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.12		0 -0.01	approx. 430	18	approx. 815	0.9	99	51	100
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.16		0 -0.01	approx. 323	14	approx. 926	0.9	99	49	100
125 <sup>3</sup> / <sub>16</sub> x 69 <sup>11</sup> / <sub>16</sub>	0.12		0 -0.01	approx. 1507	25	approx. 2866	0.9	99	51	100
125 <sup>3</sup> / <sub>16</sub> x 69 <sup>11</sup> / <sub>16</sub>	0.16		0 -0.01	approx. 1335	22	approx. 2976	0.9	99	49	100
<b>MIROGARD® plus</b>										
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 355	5 small-scale- packaging à 3 sheets, approx. 77 lbs	approx. 573	1.1	98	18 ± 2	98
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 538	23	approx. 727	1.1	98	18 ± 2	98
34 <sup>27</sup> / <sub>32</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 538	46	approx. 683	1.1	98	18 ± 2	98
34 <sup>27</sup> / <sub>32</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.08		0 -0.01	approx. 581	10 small-scale- packaging à 5 sheets, approx. 64 lbs	approx. 738	1.1	98	18 ± 2	98
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.12		0 -0.01	approx. 409	18	approx. 815	1.1	98	18 ± 2	98
125 <sup>3</sup> / <sub>16</sub> x 69 <sup>11</sup> / <sub>16</sub>	0.12		0 -0.01	approx. 1507	25	approx. 2866	1.1	98	18 ± 2	98
125 <sup>3</sup> / <sub>16</sub> x 69 <sup>11</sup> / <sub>16</sub>	0.16		0 -0.01	approx. 1335	22	approx. 2976	1.1	98	18 ± 2	98
<b>MIROGARD® Protect</b>										
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.17	4/2	0 -0.02	approx. 161	7	approx. 573	0.9	98	< 1	100
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.25	6/2	0 -0.02	approx. 161	7	approx. 683	0.9	98	< 1	100
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.33	8/2	0 -0.02	approx. 140	6	approx. 716	0.9	98	< 1	100
<b>MIROGARD® Protect Ultra</b>										
69 <sup>11</sup> / <sub>16</sub> x 48 <sup>1</sup> / <sub>32</sub>	0.12		± 0.01	approx. 409	18	approx. 683	0.9	98	< 0.05	100

\* (300 nm to 380 nm)

# SCHOTT MIROGARD® – Anti-Reflective Glass for Art Glazing

## Technical Data Sheet

### Virtually no reflections

Conventional glass reflects about 8% of light. This results in an undesirable reflection effect. With SCHOTT's optical interference coated Anti-Reflective Glass, reflection is reduced to approx. 1%, which means it is virtually eliminated.

### Highest transparency

Normal glass has light transmission of only 91%. With MIROGARD® glasses, it is close to 99%. This means that MIROGARD®, MIROGARD® plus, MIROGARD® Protect and MIROGARD® Protect Ultra are nearly invisible under normal viewing conditions. MIROGARD®, MIROGARD® Protect and MIROGARD® Protect Ultra portray the colors of the pictures glazed as neutrally as possible thanks to their high color rendering index  $R_a = 100$ . The result: The brilliance of colors in works of art is reproduced without losing any of its original quality.

### Lightweight and very thin

Because it is only 0.12 inches thick, MIROGARD® Protect Ultra can easily be used in existing standard picture framing solutions. At the time it is extremely mechanical stable and weighs only 14.33 lbs/sq ft.

### Protection from UV-radiation

All types of MIROGARD® glass reduce UV-radiation by absorption and reflection. Various versions of the product are available, depending on the level of protection required.

SCHOTT North America, Inc.  
555 Taxter Road  
Elmsford, NY 10523  
USA  
Phone +1 (914) 831-2240  
info.architecture@us.schott.com

[www.us.schott.com/mirogard](http://www.us.schott.com/mirogard)

**SCHOTT**  
glass made of ideas