# **Universal Ringlight**

For 33 to 81 mm objective diameters



Universal Ringlight A08600.1 (new clamp style)

#### **Product and Performance Characteristics**

SCHOTT ringlights emit intense, uniform, and shadow-free illumination for Microscopy and Machine Vision applications

- Fits microscope and camera objectives from 33 to 81 mm with appropriate clamps
- Working distance is 1.5" to 6" (38 to 152 mm)
- 33" (838 mm) bundle length on all models
- Two unique clamping/mounting systems for precise positioning, most ringlights fit directly onto the microscope and camera objective without adapters
- Inputs fit all ColdVision light sources; ringlights can be used with other manufacturer's continuous light sources although adapters may be necessary
- Use ringlights with our dichroic color filters, diffusers, polarizer/analyzers, and reflector rings for alternative lighting effects
- Vertical exit bundle option increases work space and prevents the bundle from interfering with surrounding objects
- Modified standard and custom ringlights are also available for your unique requirements
- · ESD (Electro Static Discharge) option is available on custom basis

## **Universal Ringlight Specifications**

Part No.	Exit	Minimum Working Distance	Objective Diameter Camera and Microscope	Mounting Clamps	Polarizer/ System Analyzer
A08600	Standard	1.5" - 6"	47 – 62 mm	Classic	A08615
A08600.1	Standard	1.5" - 6"	47 – 62 mm	New	A08615
A08620	Vertical	1.5" - 6"	47 – 62 mm	Classic	A08615



Universal Ringlight A08600 (classic clamp style)

## Holders, Clamp Rings and Anti-slip Pads

Part No.	Description		
A08614	Anti-slip ringlight clamps for ringlight models A08600, A08620. (3 clamps in package) (47 mm to 62 mm)		
A08601	(33 mm to 46 mm)		
A08601.1	Ringlight screw		
A08602	(62 mm to 81 mm)		



Anti-Slip Ringlight Clamps, A08614




Anti-Slip Ringlight Clamps, A08601



Anti-Slip Ringlight Clamps, A08602




### **Specifications**



A08620 - 47 mm / 62 mm Ringlight with vertical exit (classic clamp) Dimensions in ( ) are in mm

Ringlight Input: Black Anodized Aluminium or Conductive Finish Bundle Sheathing: PVC Covered Metal Tubing or Stainless Steel Working Distance: 1.5" to 6" (38 to 152)





Available Clamps


For A08611 Clamp Ring, A08600 and A22000 Ringlights and A08614, Set of 3 Clamps 1.8 / 2.4" (47/62)

For A08612 Clamp Ring, A08603 Ringlight and A08601, Set of 3 Clamps 1.3 / 1.8" (33/46)

For A08613 Clamp Ring, A08604 Ringlight, and A08602, Set of 3 Clamps 2.4 / 3.2" (62/81)







Lighting and Imaging SCHOTT North America, Inc. 122 Charlton Street Southbridge, MA 01550 USA

Phone: +1 (508) 765-9744 Fax: +1 (508) 765-1299 lightingimaging@us.schott.com www.us.schott.com/lightingimaging



All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.