

Input Adapters

For ACE® and DCR® Series Light Sources



Product and Performance Characteristics

SCHOTT provides a series of adapter bushings which fit into the DCR® Series and ACE® Series light sources.

The corresponding ferrule sizes they will accept, are shown below. The bushing attaches to the fiber bundle ferrule with a set screw. The bundle is then inserted into the light source receptacle. These adapters guarantee proper fiber bundle positioning in the focal plane of the lamp to receive the maximum light output.

| Part Number | Adapter | Ferrule |
|-------------|---------|----------------------|
| *A08009 | | Volpi |
| A08010 | | |
| A08013 | | SCHOTT KL Series |

* Made to order product
Dimensions in () are in mm

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.

Lighting and Imaging
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge, MA 01550
 USA
 Phone: +1 (508) 765-9744
 Fax: +1 (508) 765-1299
lightingimaging@us.schott.com
www.us.schott.com/lightingimaging

