

# Flexible Light Guides

1-branch



Flexible light guide for KL 2500 LCD



Flexible light guide single

## Features

- Flexible light guides are available in different lengths and diameters.
- Articulating arm and different holders for positioning available.
- Focusing lenses, color filters and polarizers available.

## Benefit

- High flexibility for different illumination techniques as well as remote illumination.


Cold light source **	Part No.	Type	Length	End tip Ø	End tip length	Active Ø branch	Jacketing material	Outer Ø Jacketing	Light source adapter Ø
			(L)	(E)	(l)	(b)		(D)	(F)
KL 1500 HAL KL 1600 LED KL 2500 LED KL 2500 LCD	155 101	1 br.	1000 mm 39.37"	6 mm 0.24"	20 mm 0.79"	3.0 mm 0.12"	M-PVC	6.8 mm 0.27"	10 mm 0.39"
	155 100		1000 mm 39.37"	6 mm 0.24"	20 mm 0.79"	5.0 mm 0.20"	M-PVC	9.8 mm 0.39"	10 mm 0.39"
	155 102		1600 mm 62.99"	6 mm 0.24"	20 mm 0.79"	5.0 mm 0.20"	M-PVC	9.8 mm 0.39"	10 mm 0.39"
	155 103		1000 mm 39.37"	10 mm 0.39"	20 mm 0.79"	8.0 mm 0.32"	M-PVC	14 mm 0.55"	10 mm 0.39"
	155 104		1000 mm 39.37"	10 mm 0.39"	20 mm 0.79"	9.0 mm 0.35"	M-PVC	14 mm 0.55"	10 mm 0.39"
KL 2500 LCD	250 102		1000 mm 39.37"	17 mm 0.67"	20 mm 0.79"	15 mm 0.59"	M-PVC	21.2 mm 0.84"	17 mm 0.67"
	250 103		1500 mm 59.06"	17 mm 0.67"	20 mm 0.79"	15 mm 0.59"	M-PVC	21.2 mm 0.84"	17 mm 0.67"

\*\* and discontinued KL 1500 products (KL 1500 compact, KL 1500 LCD, KL 1500 LED, KL 1500 LED Plus)


Version 09.2014



## Flexible Light Guides, 1-branch



Flexible Light Guides, 1-branch – KL 1500 LCD, KL 2500 LCD



Flexible Light Guides, 1-branch – KL 2500 LCD only

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.

SCHOTT North America, Inc.  
**Lighting and Imaging**  
 122 Charlton Street  
 Southbridge, MA 01550 USA  
 phone: +1-508-765-3211  
 fax: +1-508-764-6273  
 lightingimaging@us.schott.com  
 www.us.schott.com/lightingimaging

