

Flexible Light Guides

1-branch



Flexible light guide for KL 2500 LCD



Flexible light guide single

Features

- Flexible light guides are available in different lengths and diameters.
- Articulating arm and different holders for positioning available.
- Focusing lenses, color filters and polarizers available.

Benefit


- High flexibility for different illumination techniques as well as remote illumination.

Cold light source **	Part No.	Type	Length (L)	End tip Ø (E)	End tip length (l)	Active Ø branch (b)	Jacketing material	Outer Ø ¹ Jacketing (D)	Light source adapter Ø (F)
KL 1500 HAL KL 1600 LED KL 2500 LED KL 2500 LCD	155 101	1 br.	1000 mm 39.37"	6 mm 0.24"	20 mm 0.79"	3.0 mm 0.12"	M-PVC	6.8 mm 0.27"	10 mm 0.39"
	155 100		1000 mm 39.37"	6 mm 0.24"	20 mm 0.79"	5.0 mm 0.20"	M-PVC	9.8 mm 0.39"	10 mm 0.39"
	155 102		1600 mm 62.99"	6 mm 0.24"	20 mm 0.79"	5.0 mm 0.20"	M-PVC	9.8 mm 0.39"	10 mm 0.39"
	155 103		1000 mm 39.37"	10 mm 0.39"	20 mm 0.79"	8.0 mm 0.32"	M-PVC	14 mm 0.55"	10 mm 0.39"
	155 104		1000 mm 39.37"	10 mm 0.39"	20 mm 0.79"	9.0 mm 0.35"	M-PVC	14 mm 0.55"	10 mm 0.39"
KL 2500 LCD	250 102		1000 mm 39.37"	17 mm 0.67"	20 mm 0.79"	15 mm 0.59"	M-PVC	21.2 mm 0.84"	17 mm 0.67"
	250 103		1500 mm 59.06"	17 mm 0.67"	20 mm 0.79"	15 mm 0.59"	M-PVC	21.2 mm 0.84"	17 mm 0.67"


** and discontinued KL 1500 products (KL 1500 compact, KL 1500 LCD, KL 1500 LED, KL 1500 LED Plus)



Flexible Light Guides, 1-branch



Flexible Light Guides, 1-branch – KL 1500 LCD, KL 2500 LCD



Flexible Light Guides, 1-branch – KL 2500 LCD only

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.

SCHOTT North America, Inc.
Lighting and Imaging
 6862 Santa Teresa Blvd.
 San Jose, CA 95119 USA
 phone: +1-408-363-2100
 fax: +1-408-363-9980
 microscopy@us.schott.com
 www.us.schott.com/lightingimaging

SCHOTT
 glass made of ideas