


Darkfield Illuminator / Ringlight Adapters

Ringlight adapters for microscope objectives and darkfield lighting.



Darkfield Illuminator, Adapter, A08645 and Spacer Ring, A08644

Product and Performance Characteristics

- Fiber optic full annular ring configurations
- Dovetail adapters for a variety of microscopes attach to slide the illuminator into place under the microscope stage and avoid interference (See chart on left for adapter specifications)
- Please note that a spacer ring, A08644, is required for the A08645 model adapter
- Light exits at a nominal 20° horizontal angle and will illuminate a 1" (25.4)* diameter area
- Ringlight comes with a fixed size aperture to shield optic from light
- Working distances from .10" (2.5) to .38" (9.7)
- Optional made-to-order iris aperture allows adjustment of the darkfield spot size for light sensitive applications

Darkfield Illuminator & Accessories

Part No.	Description
* A08644	Darkfield Spacer Axio 2 for A08645 Adapter
* Made-to-order products	

Dovetail Adapters

Part No.	Description
* A08645	Dovetail Adapter for Zeiss Axioplan (see A08644)
* A08646	Dovetail Adapter for Leitz Laborlux, DMR
* A08647	Dovetail Adapter for Olympus
* A08649	Dovetail Adapter for Zeiss Axioskop
* Made-to-order products	

Version 01.2017

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.

Lighting and Imaging
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge, MA 01550
 USA
 Phone: +1 (508) 765-9744
 Fax: +1 (508) 765-1299
 lightingimaging@us.schott.com
 www.us.schott.com/lightingimaging

