


SCHOTT® Fiber Optic Faceplates



Fiber Optic Faceplates are used for high resolution 'zero thickness' image transfer applications.

Fiber Optic Faceplates can be coupled to CCD, CMOS and OLED devices to enable image intensification, remote viewing, field flattening and x-ray imaging.

Characteristics


In opto-electronic applications, coated faceplates are used as both input and output high resolution image transfer windows.

- Variety of sizes up to 320 x 320 mm.
- Fiber size from 2.5 μm to 25 μm or larger in fiber diameter.
- Core/clad options to vary transmission and contrast.
- Hermetically tight.
- Radiation-hardened materials available.
- Faceplate sizes are intended to serve the digital x-ray market as well as displays for commercial and defense applications.

Your Advantages

In some applications, the x-ray absorption properties of the fiber optic plates protect the photodetectors from damage and prevent electronic noise affecting the images.

- All SCHOTT faceplates are fabricated to customer-specific requirements.
- Faceplates are of a single piece construction (no tiling)
- Typical shapes are round or rectangular.



Glass Compositions for Faceplates

Glass Type										
Typical Performance Parameters	47A	47A HT	47ARH Radiation hardened	RFG 88	24A	24AS	24C	74 HR	75A	75C
Fiber size (µm)/Resolution lp/mm**	6/102 4/128	6/83	6/102 12/32	6/102 4/128	25/23 10/64 8/72 6/102	8/72 6/102 4/128 2.5/203	10/64 6/102 4/128	6/96	27/23	6/102
Numerical Aperture	1.0	1.0	1.0	0.88	1.0	1.0	1.0	1.0	0.58	0.58
Stray Light Control (EMA)	Yes	Yes	Yes	Yes	Yes	Yes	No	Yes	Yes	No
Collimated Transmission @ 550nm (3 mm)	73	85	69	73	70	75	86	65	60	95
Coefficient of Thermal Expansion (x10 ⁻⁷ /°C)	68	70	68	63	68	68	68	87	61	61
Density (g/cm ³)	4.15	4.5	4.15	3.41	4.0	4.0	4.0	4.1	3.05	3.05
Core/Clad Ratio	75/25	90/10	75/25 90/10	70/30	70/30	70/30	70/30	65/35	60/40	75/25
Lead Free	Yes	Yes	Yes	Yes	No	No	No	Yes	Yes	Yes
Phosphor Compatible	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Maximum Square Formats (mm)	320	320	320	320	320	320	320	150	320	320

** Resolution Measurement performed with a 1951 USAF Resolution Target using diffuse white light illumination. Resolution may vary with other wavelengths.

All specifications are subject to change without prior notice.
This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.
© SCHOTT North America, Inc.

Lighting and Imaging
SCHOTT North America, Inc.
122 Charlton Street
Southbridge, MA 01550
USA
Phone: +1 (508) 765-9744
Fax: +1 (508) 765-1299
lightingimaging@us.schott.com
www.us.schott.com/lightingimaging

