

Ringlight Reflector Rings / Ringlight Accessories



Reflector Ring, A08616

Ringlight Reflector Rings Characteristics

- For use with Universal and 66mm Ringlights
- Reflector ring illuminates scratches on reflective surfaces.
- The A08616 reflector ring fits the Universal and 66 mm series ringlights
- Two separate parts are included, the black anodized retaining ring and the mirror polished reflector ring, the reflector ring drops inside the retaining ring which snap-fits onto the ringlight

Part No.	Ringlights
A08616	A08600, A08603, A08604, A08620, A08625, A08680, A08600.1



Anti-Slip Ringlight Clamps, A08614

Ringlight Clamp Accessories

Dimensions in () are in mm

- Use to fix ringlight position
- Clamp(s) for A08611 clamp ring, A08600 and A22000 ringlights and A08614. Set of 3 clamps 1.8 / 2.4" (47/62)

A08614

Clamps with Anti-slip pads (set of 3)



Part No.	Description
A08614	Anti-slip Ringlight Clamps for ringlight models A08600, A08620. (3 clamps in package)

Version 01.2017

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT North America, Inc.

Lighting and Imaging
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge, MA 01550
 USA
 Phone: +1 (508) 765-9744
 Fax: +1 (508) 765-1299
 lightingimaging@us.schott.com
 www.us.schott.com/lightingimaging

