

ROBAX® Magic with Signature Impressions

Every impression is a lasting one with ROBAX® Magic.



Interior panelling ROBAX® Magic black (smooth)



ROBAX® Magic black (nubbed)

Technical Data	
Maximum usable area	1,180 x 590 mm
Glass thickness	4 mm
Recommended application	Gas fireplaces
Material colors	ROBAX® Magic black, ROBAX® Magic grey, ROBAX® Magic translucent bluegrey, ROBAX® Magic white, ROBAX® Magic translucent white, ROBAX® Magic transparent
Shapes	Flat
Surface structure	Smooth, nubbed, grooved, grooved inverse
Decoration	On request
Cleaning	SCHOTT ROBAX® Dry Wiper

Thermal Characteristics	
Temperature resistance	400 to 610 °C (752 to 1,130 °F) = 1,000 hours 425 to 660 °C (797 to 1,220 °F) = 100 hours
Thermal shock resistance	$T_{max} \leq 650 \text{ °C (1.202 °F)}$
Resistance to temperature differences (RDT)	$T_{max} \leq 650 \text{ °C (1.202 °F)}$ Attention: ROBAX® Magic grey and translucent bluegrey: $T_{max} \leq 450 \text{ °C (842 °F)}$

Chemical Characteristics	
Acid resistance	min. Class S2 (acc. to DIN 12116)
Alkaline resistance	min. Class A2 (in line with ISO 695)
Hydrolytic resistance	HGB 1 (acc. to ISO 719)



50149 ENGLISH/US 01/2019 all/nino Printed in Germany

SCHOTT North America, Inc.
5530 Shepherdsville Road
Louisville, KY 40228
USA
Phone (800)822-0600
info.robax@us.schott.com

www.us.schott.com/robax

SCHOTT
ROBAX®