

SCHOTT Standard product range

American sizes

Tubing

Outer diameter	Wall thickness	Description sw/mw/hw	Carton contents		Pallet load	
 mm	 mm	 59 inch length	 Number of tubes	Weight approx. kg	 Number of cartons	Weight approx. kg
8.0 ±0.13	2.0 ±0.11	5/16" hw	154	42.77	27	1154.78
9.5 ±0.13	2.0 ±0.13	3/8" hw	108	37.48	27	1011.92
12.7 ±0.16 ±0.20	1.6 ±0.08 2.4 ±0.15	1/2" mw 1/2" hw	72 42	29.54 24.03	35 45	1033.97 1081.37
15.9 ±0.16 ±0.16	1.6 ±0.08 2.4 ±0.12	5/8" mw 5/8" hw	56 56	29.76 42.11	35 28	1041.68 1179.03
22.0 ±0.23	1.5 ±0.08	7/8" sw	42	29.98	35	1049.4
22.2 ±0.30	3.2 ±0.18	7/8" hw	30	42.33	28	1185.2
25.4 ±0.25 ±0.23 ±0.30	1.5 ±0.10 2.5 ±0.12 4.0 ±0.25	1" sw 1" mw 1" hw	25 25 20	20.72 33.07 39.68	35 35 28	725.32 1157.43 1111.13
31.7 ±0.30	2.4 ±0.14	1 1/4" mw	16	26.01	35	910.51
31.8 ±0.30 ±0.40	2.4 ±0.14 4.0 ±0.25	1 1/4" mw 1 1/4" hw	16 16	26.23 41.23	35 28	918.22 1154.34
38.1 ±0.45	4.0 ±0.25	1 1/2" hw	9	28.44	35	995.39
45.0 ±0.70	2.0 ±0.15	1 7/10" sw	16	31.97	20	639.34
50.8 ±0.65	3.2 ±0.22	2" mw	9	31.75	20	634.93
51.0 ±0.65	2.0 ±0.11	2" sw	9	20.50	20	410.06
57.1 ±0.65	3.2 ±0.22	2 1/4" mw	9	35.94	20	718.71
63.5 ±0.75	4.8 ±0.30	2 1/2" hw	4	26.01	35	910.51
76.2 ±0.85	3.2 ±0.18	3" mw	4	21.61	20	432.11
88.9 ±1.10	4.8 ±0.35	3 1/2" hw	4	37.48	20	749.57
100.0 ±1.30	2.4 ±0.16	4" sw	4	21.61	20	432.11
107.25 ±1.70	3.0 ±0.50	4 1/5" mw	3	21.83	12	261.91
114.3 ±1.40	4.8 ±0.45	4 1/2" mw	2	24.25	15	363.76

Tubing
 SCHOTT North America, Inc.
 555 Taxter Road
 Elmsford, NY 10523
 USA
 Phone (914) 831-2200
 Fax (914) 831-2201
 Info.tubing@us.schott.com

www.us.schott.com/tubing

SCHOTT
 glass made of ideas