

# Product Range

## Borosilicate Glass Bends



Outside Diameter		Wall Thickness		U-Bend Width		U-Bend Height		Straight Side Length			
mm	in	mm	in	mm	in	mm	in	mm ±	in ±		
56 ± 0.9	2.20 ± 0.04	2.5 ± 0.3	0.10 ± 0.01	236 ± 2.0	9.29 ± 0.08	180 ± 10.0	7.09 ± 0.39	50	+ 10.0 - 0.0	1.97	+ 0.39 - 0.00
65 ± 1.0	2.56 ± 0.04	2.8 ± 0.3	0.11 ± 0.01	245 ± 2.0	9.65 ± 0.08	180 ± 10.0	7.09 ± 0.39	45	+ 10.0 - 0.0	1.77	+ 0.39 - 0.00

Other shapes and dimensions available upon request.