









Product Range

Borosilicate Glass Tubing

Tubes up to 10 m in length



Outside Diameter		Wall Thickness		Tube Length		Weight per Tube		Package Content		
										
mm	in	mm	in	m	in	kg	lb	Number of Tubes	Weight approx. kg	Weight approx. lb
56 ± 0.9	2.20 ± 0.04	1.8 ± 0.3	0.07 ± 0.01	1.4	55.1	0.96	2.11	9	9	19
				5.5	216.5	3.76	8.28	168	631	1,392
				10.0	393.7	6.83	15.06	104	710	1,566
65 ± 1.0	2.56 ± 0.04	2.2 ± 0.3	0.09 ± 0.01	1.4	55.1	1.35	2.99	8	11	24
				5.5	216.5	5.32	11.73	120	638	1,408
				10.0	393.7	9.67	21.33	84	813	1,792
300 ± 3.8	11.81 ± 0.15	5.0 ± 0.8	0.20 ± 0.03	1.3	51.2	13.43	29.60	9	121	266
				4.0	157.5	41.31	91.08	9	372	820

Other dimensions and quantities available upon request.