

N-SF1
717296.303

$n_d = 1,71736$	$v_d = 29,62$	$n_F - n_C = 0,024219$
$n_e = 1,72308$	$v_e = 29,39$	$n_F' - n_C' = 0,024606$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,67021
$n_{1970,1}$	1970,1	1,67641
$n_{1529,6}$	1529,6	1,68350
$n_{1060,0}$	1060,0	1,69240
n_i	1014,0	1,69358
n_e	852,1	1,69889
n_f	706,5	1,70651
n_C	656,3	1,71035
$n_{C'}$	643,8	1,71144
$n_{632,8}$	632,8	1,71247
n_D	589,3	1,71715
n_d	587,6	1,71736
n_e	546,1	1,72308
n_F	486,1	1,73457
$n_{F'}$	480,0	1,73605
n_g	435,8	1,74919
n_h	404,7	1,76224
n_i	365,0	
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel	
B_1	1,60865158
B_2	0,237725916
B_3	1,515306530
C_1	0,01196548790
C_2	0,0590589722
C_3	135,5216760

Konstanten der Formel für dn/dT	
D_0	-3,72E-06
D_1	8,05E-09
D_2	-1,71E-11
E_0	8,98E-07
E_1	1,34E-09
λ_{TK} [μ m]	0,276

Temperaturkoeffizienten der Lichtbrechung						
[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060.0	e	g	1060.0	e	g
-40/-20	0,1	1,7	3,6	-2,2	-0,7	1,2
+20/+40	0,0	1,8	4,2	-1,5	0,3	2,7
+60/+80	0,0	2,1	4,8	-1,1	0,9	3,5

Reintransmissionsgrad τ_i		
λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0,730	0,460
2325	0,800	0,580
1970	0,940	0,850
1530	0,989	0,973
1060	0,998	0,995
700	0,996	0,990
660	0,994	0,986
620	0,995	0,987
580	0,996	0,990
546	0,994	0,986
500	0,987	0,968
460	0,976	0,940
436	0,963	0,910
420	0,950	0,870
405	0,900	0,760
400	0,870	0,700
390	0,770	0,520
380	0,570	0,250
370	0,250	0,030
365	0,100	
350		
334		
320		
310		
300		
290		
280		
270		
260		
250		

Farbcode	
$\lambda_{80} / \lambda_{5}$	41/36

Bemerkungen	
(*= λ_{70}/λ_5)	

Relative Teildispersionen	
$P_{s,t}$	0,2190
$P_{C,s}$	0,4733
$P_{d,c}$	0,2895
$P_{e,d}$	0,2360
$P_{g,F}$	0,6037
$P_{i,h}$	
$P'_{s,t}$	0,2156
$P'_{C,s}$	0,5103
$P'_{d,c'}$	0,2405
$P'_{e,d}$	0,2323
$P'_{g,F'}$	0,5340
$P'_{i,h}$	

Abweichung relativer Teildispersionen ΔP von der "Normalgeraden"	
$\Delta P_{C,t}$	0,0068
$\Delta P_{C,s}$	0,0013
$\Delta P_{F,e}$	0,0016
$\Delta P_{g,F}$	0,0097
$\Delta P_{i,g}$	

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C}$ [$10^{-6}/K$]	9,1
$\alpha_{+20/+300^\circ C}$ [$10^{-6}/K$]	10,5
T_g [°C]	553
T_{10}^{13} [°C]	554
$T_{10}^{7,6}$ [°C]	660
c_p [J/(g·K)]	0,750
λ [W/(m·K)]	1,000
ρ [g/cm ³]	3,03
E [10^3 N/mm ²]	90
μ	0,250
K [10^{-6} mm ² /N]	2,72
$HK_{0,1/20}$	540
HG	5
CR	1
FR	0
SR	1
AR	1
PR	1